

Double-membrane seals

DMS M20/sw



DMS M20/sw

Double-membrane seals

Productnumber: 26002001

Dimensions: 25,2 x 25,2 x 13,4 mm

Double membrane seals, IP66, with two sealing membranes, closed, thermoplastic elastomer (TPE), for wall thicknesses 1.5 - 4.5 mm, black

Sealing range 7 - 13 mm



Technical Data

electrical characteristics

Type of protection:	IP66
---------------------	------

Colours

Accessory colour:	deep black
-------------------	------------

Dimensions

Width:	25.2 mm
--------	---------

Length:	25.2 mm
---------	---------

Height:	13.4 mm
---------	---------

Nominal size:	M20
---------------	-----

Material characteristics

UV-resistant:	yes
---------------	-----

Halogen free:	yes
---------------	-----

Industry quality:	no
-------------------	----

mechanical properties

for sealing range min:	7 mm
------------------------	------

for sealing range max:	13 mm
------------------------	-------

Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------

Material

Accessory material:	Rubber
---------------------	--------
