

Double-membrane seals

## DMS M32/sw



### DMS M32/sw

#### Double-membrane seals

Productnumber: 26003201

Dimensions: 36,7 x 36,7 x 14,7 mm

Double membrane seals, IP66, with two sealing membranes, closed, thermoplastic elastomer (TPE), for wall thicknesses 1.5 - 4.5 mm, black

**Sealing range 13 - 21 mm**



---

## Technical Data

### electrical characteristics

---

Type of protection:	IP66
---------------------	------

---

### Colours

---

Accessory colour:	deep black
-------------------	------------

---

### Dimensions

---

Width:	36.7 mm
--------	---------

---

Length:	36.7 mm
---------	---------

---

Height:	14.7 mm
---------	---------

---

Nominal size:	M32
---------------	-----

---

### Material characteristics

---

UV-resistant:	yes
---------------	-----

---

Halogen free:	yes
---------------	-----

---

Industry quality:	no
-------------------	----

---

### mechanical properties

---

for sealing range min:	13 mm
------------------------	-------

---

for sealing range max:	21 mm
------------------------	-------

---

### Ambient conditions

---

Installation location:	protected outdoor areas
------------------------	-------------------------

---

### Material

---

Accessory material:	Rubber
---------------------	--------

---