

Double-membrane seals

## DMS M20/w



### DMS M20/w

#### Double-membrane seals

Productnumber: 26012001

Dimensions: 25,2 x 25,2 x 13,4 mm

Double membrane seals, IP66, with two sealing membranes, closed, thermoplastic elastomer (TPE), for wall thicknesses 1.5 - 4.5 mm, white

**Sealing range 7 - 13 mm**



---

## Technical Data

### electrical characteristics

---

Type of protection:	IP66
---------------------	------

---

### Colours

---

Accessory colour:	clear white
-------------------	-------------

---

### Dimensions

---

Width:	25.2 mm
Length:	25.2 mm
Height:	13.4 mm
Nominal size:	M20

---

### Material characteristics

---

UV-resistant:	yes
Halogen free:	yes
Industry quality:	no

---

### mechanical properties

---

for wall thickness max:	4.5 mm
for sealing range min:	7 mm
for sealing range max:	13 mm
for wall thickness min:	1.5 mm

---

### Ambient conditions

---

Installation location:	protected outdoor areas
------------------------	-------------------------

---

### Material

---

Accessory material:	Rubber
---------------------	--------

---