

Double-membrane seals

DMS M25



DMS M25

Double-membrane seals

Productnumber: 26042501

Dimensions: 29,7 x 29,7 x 13,6 mm

Double membrane seals, IP66, with two sealing membranes, closed, thermoplastic elastomer (TPE), for wall thicknesses 1.5 - 4.5 mm, grey

Sealing range 9 - 17 mm



Technical Data

electrical characteristics

Type of protection:	IP66
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	29.7 mm
--------	---------

Length:	29.7 mm
---------	---------

Height:	13.6 mm
---------	---------

Nominal size:	M25
---------------	-----

Material characteristics

UV-resistant:	yes
---------------	-----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	HB
-----------------------------------------	----

Glow-wire flammability according to EN 60695-2-11:	750 °C
----------------------------------------------------	--------

Industry quality:	no
-------------------	----

mechanical properties

for sealing range min:	9 mm
------------------------	------

for sealing range max:	17 mm
------------------------	-------

Type of accessory:	other
--------------------	-------

Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------

Material

Accessory material:	Rubber
---------------------	--------
