

Double-membrane seals

DMS M40



DMS M40

Double-membrane seals

Productnumber: 26044001

Dimensions: 46,5 x 46,5 x 18,6 mm

Double membrane seals, IP66, with two sealing membranes, closed, thermoplastic elastomer (TPE), for wall thicknesses 1.5 - 4.5 mm, grey

Sealing range 17 - 28 mm



Technical Data

electrical characteristics

Type of protection:	IP66
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	46.5 mm
--------	---------

Length:	46.5 mm
---------	---------

Height:	18.6 mm
---------	---------

Nominal size:	M40
---------------	-----

Material characteristics

UV-resistant:	yes
---------------	-----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	HB
---	----

Glow-wire flammability according to EN 60695-2-11:	750 °C
--	--------

Industry quality:	no
-------------------	----

mechanical properties

for sealing range min:	17 mm
------------------------	-------

for sealing range max:	28 mm
------------------------	-------

Type of accessory:	other
--------------------	-------

Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------