

Conduit connector

RST M20-19



RST M20-19

Conduit connector

Productnumber: 28842201

Dimensions: 29 x 26 x 38 mm

Pipe socket to take smooth pipes, with locknut,
polystyrene, grey

for conduits with an external diameter of 19 mm



Technical Data

electrical characteristics

Type of protection:	IP54
---------------------	------

Colours

Accessory colour:	light grey
-------------------	------------

Dimensions

Width:	29 mm
--------	-------

Length:	26 mm
---------	-------

Height:	38 mm
---------	-------

Material characteristics

UV-resistant:	no
---------------	----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	HB
---	----

Glow-wire flammability according to EN 60695-2-11:	650 °C
--	--------

Industry quality:	no
-------------------	----

Ambient conditions

Installation location:	Indoors
------------------------	---------
