

Junction box

AP 7 - 2,5²



AP 7 - 2,5²

Junction box

Productnumber: 31510701

Dimensions: 78 x 78 x 27 mm

Junction box, protection class IP30, nominal cross-section 2.5 mm², U_i=400 V AC, certified by VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22)), knockouts, (1 rear, 7 side), internal fixing points, for standard indoor installations

grey, I_n=24 A, with 5 interlockable screw terminals 2.5 mm² (5 x 1² / 5 x 1.5² / 3 x 2.5²)



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Max. conductor cross section:	2,5 mm ²
Protection class:	II
Type of protection:	IP30
UL Type Rating:	not specified

Colours

Base unit colour:	grey
Cover colour:	grey

Dimensions

Width:	78 mm
Length:	78 mm
Height:	27 mm

Material characteristics

UV-resistant:	no
Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK07
Sealable:	no
Fastening:	internal fixing points

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	Indoors

Material

Base unit material:	Polypropylene
Cover material:	Polypropylene
Cover screw material:	Polycarbonate

Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
------------	---

Accessories

[68502001 - HandyGrip VG 20 - Terminal strip](#)

[68502101 - HandyGrip VG 21 - Terminal strip](#)

[68512101 - HandyGrip VG 21 w - Terminal strip](#)

[68832001 - HandyQuick SQ 32 - Screwless terminal](#)

[68852001 - HandyQuick SQ 52 - Screwless terminal](#)

Cable gland

