

Junction box

HP 80-L



HP 80-L

Junction box

Productnumber: 32298001

Dimensions: 85 x 85 x 42 mm

Junction box, protection class IP55, nominal cross-section 2.5 mm², U_i=400 V AC, certified by VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22)), stepped nipple, M20, sealing range 5 - 16 mm, (1 rear, 7 side), internal fixing points, for standard indoor installations

grey, without terminals



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Max. conductor cross section:	2,5 mm ²
Protection class:	II
Type of protection:	IP55
UL Type Rating:	not specified

Colours

Base unit colour:	grey
Cover colour:	grey

Dimensions

Width:	85 mm
Length:	85 mm
Height:	42 mm
Inner length:	78 mm
Inner width:	78 mm
Inner height:	38 mm

Material characteristics

UV-resistant:	no
Halogen free:	no
Industry quality:	no

mechanical properties

for sealing range min:	5 mm
for sealing range max:	16 mm
Type of fastening:	Wall/ceiling mounting
Impact strength:	IK07
Sealable:	no
Fastening:	internal fixing points

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	Indoors

Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
------------	---

Accessories

[22742001 - KVR M20-MGM - Cable gland](#)

[22742101 - KVR M20-GDB/MGM - Cable gland](#)

[26012001 - DMS M20/w - Double-membrane seals](#)

[26042001 - DMS M20 - Double-membrane seals](#)

[84000401 - Abox 025/040 KLS-2.5²/4² - Terminal block](#)

Cable gland

