

Strain relief

ZEL 2K-12

This product is outdated. To the successor product: <https://www.spelsberg.com/p/34400201>



ZEL 2K-12

Strain relief

Productnumber: 34400101

Dimensions: 28 x 73 x 16 mm

Strain relief, for assembly in 2K-12 / 2K-16-junction boxes, strain relief possible for up to 2 entries, strain relief can be split without tools, 2 strain relief clamps are required for T wiring

Grey

Technical Data

Dimensions

| | |
|---------|-------|
| Width: | 28 mm |
| Length: | 73 mm |
| Height: | 16 mm |

Material characteristics

| | |
|--|--------|
| Flammability class according with UL94: | HB |
| Glow-wire flammability according to EN 60695-2-11: | 750 °C |
| Industry quality: | no |

mechanical properties

| | |
|--------------------|---------------|
| Type of accessory: | Strain relief |
|--------------------|---------------|