

Channel installation box

KD 2 70/44 F2 gn

KD 2 70/44 F2 gn


Channel installation box

Productnumber: 36240401

Dimensions: 47 mm

Channel installation box, rated insulation voltage:
400V AC, certified by VDE (DIN EN 50085-1 (VDE
0604-1))

**2-way, for installation in Niedax wall
trunkings/device installation ducts**



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
------------------------------	-------

Colours

Cover colour:	grey
---------------	------

Dimensions

Height:	47 mm
---------	-------

Material characteristics

Halogen free:	no
---------------	----

Industry quality:	no
-------------------	----

Ambient conditions

max. relative humidity 25°C:	100 %
------------------------------	-------

max. relative humidity 40°C:	50 %
------------------------------	------

Min. ambient temperature:	-25 °C
---------------------------	--------

Max. ambient temperature:	40 °C
---------------------------	-------

24h ambient temperature:	35 °C
--------------------------	-------

Installation location:	Indoors
------------------------	---------

Material

Base unit material:	Polypropylene
---------------------	---------------

Cover material:	Polypropylene
-----------------	---------------

Certificates

Test mark:	VDE (DIN EN 50085-1 (VDE 0604-1))
------------	-----------------------------------
