

Junction box

Abox-i 350-35²

This product is outdated. To the successor product: <https://www.spelsberg.com/p/43542001>



Abox-i 350-35²

Junction box

CUSTOMIZABLE

Productnumber: 49043501

Dimensions: 250 x 250 x 115 mm

Junction box, protection class IP65, nominal cross-section 35 mm², U_i=690 V AC, certified by VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22)), DLG (Ammonia resistance), DNV (Class: Ships and Offshore Installations), knockouts, M25/M32/M40/M50, (2 rear, 12 side), internal fixing points, for installations in industrial environments and protected outdoor areas

grey, with raised screw terminal, 5-pole - 35 mm²
(4 x 10² / 4 x 16² / 4 x 25² / 4 x 35²)

Accessories supplied:
1 Sealing kit



Technical Data

electrical characteristics

Rated insulation voltage AC:	690 V
Max. conductor cross section:	35 mm ²
Protection class:	II
Type of protection:	IP65
UL Type Rating:	not specified

Colours

Base unit colour:	grey
Cover colour:	grey

Dimensions

Width:	250 mm
Length:	250 mm
Height:	115 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK08
Sealable:	yes
Cover screw torque:	1.7 Nm
Fastening:	internal fixing points

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Installation location:	protected outdoor areas

Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate, glass-fibre reinforced
Sealing material:	Polyurethane
Cover screw material:	Stainless steel V2A

Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
Test mark:	DLG (Ammonia resistance)
Test mark:	DNV (Class: Ships and Offshore Installations)

Accessories

- [22742101 - KVR M20-GDB/MGM - Cable gland](#)
- [22742501 - KVR M25-MGM - Cable gland](#)
- [22743201 - KVR M32-MGM - Cable gland](#)
- [22744001 - KVR M40-MGM - Cable gland](#)
- [22745001 - KVR M50-MGM - Cable gland](#)
- [26012001 - DMS M20/w - Double-membrane seals](#)
- [26012501 - DMS M25/w - Double-membrane seals](#)
- [26042001 - DMS M20 - Double-membrane seals](#)
- [26042501 - DMS M25 - Double-membrane seals](#)
- [26043201 - DMS M32 - Double-membrane seals](#)
- [26044001 - DMS M40 - Double-membrane seals](#)
- [19202501 - KS M25 - Combi set](#)
- [19202601 - KS M25-gro - Combi set](#)
- [26202001 - BST M20/sw - Ventilation seal](#)
- [26242001 - BST M20 - Ventilation seal](#)
- [28842001 - RST M20 - Conduit connector](#)
- [68502001 - HandyGrip VG 20 - Terminal strip](#)
- [68502101 - HandyGrip VG 21 - Terminal strip](#)
- [68512101 - HandyGrip VG 21 w - Terminal strip](#)
- [68832001 - HandyQuick SQ 32 - Screwless terminal](#)
- [68852001 - HandyQuick SQ 52 - Screwless terminal](#)
- [84003501 - Abox 250/350 KLS-25²/35² - Terminal block](#)

Cable gland

