

Junction box

Abox-i 040-L/sw

This product is outdated. To the successor product: <https://www.spelsberg.com/p/40400001>



Abox-i 040-L/sw

Junction box

CUSTOMIZABLE

Productnumber: 49190401

Dimensions: 93 x 93 x 55 mm

Junction box, protection class IP65, nominal cross-section 4 mm², Ui=690 V AC, certified by VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22)), DLG (Ammonia resistance), DNV (Class: Ships and Offshore Installations), self-sealing, soft insertion membranes, M20, sealing range 2 - 16 mm, (1 rear, 7 side), internal fixing points, for installations in industrial environments and protected outdoor areas

black, without terminals



Technical Data

electrical characteristics

Rated insulation voltage AC:	690 V
Max. conductor cross section:	4 mm ²
Protection class:	II
Type of protection:	IP65
UL Type Rating:	not specified

Colours

Base unit colour:	black
Cover colour:	black

Dimensions

Width:	93 mm
Length:	93 mm
Height:	55 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	yes

mechanical properties

for sealing range min:	2 mm
for sealing range max:	16 mm
Type of fastening:	Wall/ceiling mounting
Impact strength:	IK08
Sealable:	yes
Cover screw torque:	1.7 Nm

mechanical properties

Fastening:	internal fixing points
------------	------------------------

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Installation location:	protected outdoor areas

Material

Base unit material:	ASA-PC
Cover material:	ASA-PC
Sealing material:	Thermoplastic elastomer
Cover screw material:	Stainless steel V2A

Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
Test mark:	DLG (Ammonia resistance)
Test mark:	DNV (Class: Ships and Offshore Installations)

Accessories

[20302001 - WST M20/sw - Twist plug](#)

[21302001 - WNI M20/sw - Twist nipple](#)

[22702001 - KVR M20-MGM/sw - Cable gland](#)

[22702101 - KVR M20-GDB/MGM/sw - Cable gland](#)

[26002001 - DMS M20/sw - Double-membrane seals](#)

[26202001 - BST M20/sw - Ventilation seal](#)

[26242001 - BST M20 - Ventilation seal](#)

[84000401 - Abox 025/040 KLS-2,5²/4² - Terminal block](#)

[84000201 - Abox 025/040 KLH-SL 0,2/4² - Terminal holder](#)

Cable gland

