

Junction box

## Abox-i m 040 AB SB-L



### Abox-i m 040 AB SB-L

Junction box

CUSTOMIZABLE

Productnumber: 50370401

Dimensions: 94 x 94 x 57 mm

Junction box, protection class IP66, nominal cross-section 4 mm<sup>2</sup>, Ui=690 V AC, certified by VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22)), DLG (Ammonia resistance), DNV (Class: Ships and Offshore Installations), knockouts, M20/M25, (1 rear, 8 side), external fixing lugs, for installations in industrial environments and protected outdoor areas

**grey, with red cover, without terminals, for identifying circuits for safety lighting**

**Accessories supplied:**

**4 Double-membrane seal IP66 M25 sealing range 9 - 16 mm**



## Technical Data

### electrical characteristics

Rated insulation voltage AC:	690 V
Max. conductor cross section:	4 mm <sup>2</sup>
Protection class:	II
Type of protection:	IP66
UL Type Rating:	not specified

### Colours

Base unit colour:	grey
Cover colour:	red

### Dimensions

Width:	94 mm
Length:	94 mm
Height:	57 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

### mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK08
Sealable:	yes
Cover screw torque:	1.7 Nm
Fastening:	external fixing lugs

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Installation location:	protected outdoor areas

### Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate, glass-fibre reinforced
Sealing material:	Thermoplastic elastomer
Cover screw material:	Stainless steel V2A

### Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
Test mark:	DLG (Ammonia resistance)
Test mark:	DNV (Class: Ships and Offshore Installations)

## Accessories

[22742001 - KVR M20-MGM - Cable gland](#)

[22742101 - KVR M20-GDB/MGM - Cable gland](#)

[22742501 - KVR M25-MGM - Cable gland](#)

[24742501 - KVR M25 - Cable gland](#)

[26012001 - DMS M20/w - Double-membrane seals](#)

[26012501 - DMS M25/w - Double-membrane seals](#)

[26042001 - DMS M20 - Double-membrane seals](#)

[26042501 - DMS M25 - Double-membrane seals](#)

[84000401 - Abox 025/040 KLS-2,5<sup>2</sup>/4<sup>2</sup> - Terminal block](#)

[84000201 - Abox 025/040 KLH-SL 0,2/4<sup>2</sup> - Terminal holder](#)

## Cable gland

