

Hinged window

KF 12

KF 12

Hinged window

Productnumber: 56741201

Dimensions: 228 x 80 x 24,2 mm

Hinged window, for fitting to enclosure cover, for maximum 12 modules à 17.5 mm, with transparent hinged window, frame with sealing on both sides, with drilling template and fixing screws

IP65



Technical Data

electrical characteristics

Type of protection:	IP65
---------------------	------

Dimensions

Width:	228 mm
--------	--------

Length:	80 mm
---------	-------

Height:	24.2 mm
---------	---------

Material characteristics

Flammability class according with UL94:	V2
---	----

Glow-wire flammability according to EN 60695-2-11:	960 °C
--	--------

Industry quality:	no
-------------------	----

mechanical properties

Type of accessory:	other
--------------------	-------

Ambient conditions

Installation location:	protected outdoor areas
------------------------	-------------------------
