

Enclosure with sliding seal

SVi LS-g



SVi LS-g

Enclosure with sliding seal

Productnumber: 59112201

Dimensions: 150 x 300 x 137 mm

Empty enclosure - Industrial Quality -, with sliding seal and cable clamp



Technical Data

electrical characteristics

Rated operating voltage AC:	400 V
Protection class:	II
Type of protection:	IP54
UL Type Rating:	not specified

Dimensions

Width:	150 mm
Length:	300 mm
Height:	137 mm
Inner height:	119 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

mechanical properties

Type of fastening:	Surface mounted
Impact strength:	IK07

Ambient conditions

Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Installation location:	protected outdoor areas

Material

Base unit material:	Plastic
---------------------	---------

Cable gland

