

Empty enclosure

## SVi LQ-t



### SVi LQ-t

#### Empty enclosure

Productnumber: 59121001

Dimensions: 150 x 150 x 137 mm

Empty enclosure - Industrial Quality -, for individual expansion with standard rails or mounting plates

**IP65, protective insulation, box + lid  
polycarbonate, box grey, simil. RAL 7035, cover,  
transparent**



## Technical Data

### electrical characteristics

Rated operating voltage AC:	400 V
Protection class:	II
Type of protection:	IP65
UL Type Rating:	not specified

### Colours

Base unit colour:	grey
-------------------	------

### Dimensions

Width:	150 mm
Length:	150 mm
Height:	137 mm
Inner length:	140 mm
Inner width:	140 mm
Inner height:	119 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

### mechanical properties

Type of fastening:	Surface mounted
Impact strength:	IK07

### Ambient conditions

max. relative humidity 25°C:	95 %
------------------------------	------

### Ambient conditions

max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Installation location:	protected outdoor areas

### Material

Base unit material:	Plastic
Cover material:	Polycarbonate

## Cable gland

