

Empty enclosure

SVi LQ-g



SVi LQ-g

Empty enclosure

Productnumber: 59122001

Dimensions: 150 x 150 x 137 mm

Empty enclosure - Industrial Quality -, for individual expansion with standard rails or mounting plates

**IP65, protective insulation, box + lid
polycarbonate, grey, simil. RAL 7035**



Technical Data

electrical characteristics

Rated operating voltage AC:	400 V
Protection class:	II
Type of protection:	IP65
UL Type Rating:	not specified

Colours

Base unit colour:	grey
-------------------	------

Dimensions

Width:	150 mm
Length:	150 mm
Height:	137 mm
Inner length:	140 mm
Inner width:	140 mm
Inner height:	119 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

mechanical properties

Type of fastening:	Surface mounted
Impact strength:	IK07

Ambient conditions

max. relative humidity 25°C:	95 %
------------------------------	------

Ambient conditions

max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Installation location:	protected outdoor areas

Material

Base unit material:	Plastic
Cover material:	Polycarbonate

Cable gland

