

Terminal block enclosure

RKKi 4/05-5x4²



RKKi 4/05-5x4²

Terminal block enclosure

CUSTOMIZABLE

Productnumber: 63540401

Dimensions: 94 x 65 x 57 mm

Terminal block enclosure, protection class IP54/IP66, nominal cross-section 4 mm², Ui=400V AC, Polycarbonate, internal fixing points, for installations in industrial environments and protected outdoor areas

equipped with 5-pole terminal block 4mm²
(Contaclip BKA 4 type)

Accessories supplied:
3 attachment bushes IP54 M20 seal range 8 - 13,5 mm



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Max. conductor cross section:	4 mm ²
Protection class:	II
Type of protection:	IP54/IP66
UL Type Rating:	not specified

Dimensions

Width:	94 mm
Length:	65 mm
Height:	57 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK08
Sealable:	yes
Stackable:	yes
Fastening:	internal fixing points

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C

Ambient conditions

Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced

Accessories

[19000101 - HBA - Mounting material](#)

[19000201 - ASS-kl - External hinge set](#)

[19202001 - KS M20 - Combi set](#)

[19400101 - TK ABL - External fixing lugs kit](#)

Cable gland

