

Terminal block enclosure

RKKi 4/10-10x4²



RKKi 4/10-10x4²

Terminal block enclosure

CUSTOMIZABLE

Productnumber: 63740401

Dimensions: 94 x 94 x 57 mm

Terminal block enclosure, protection class IP54/IP66, nominal cross-section 4 mm², Ui=400V AC, Polycarbonate, internal fixing points, for installations in industrial environments and protected outdoor areas

equipped with 10-pole terminal block 4mm² (Contaclip BKA 4 type)

Accessories supplied:
4 attachment bushes IP54 M20 seal range 8 - 13,5 mm



Technical Data

electrical characteristics

| | |
|-------------------------------|-------------------|
| Rated insulation voltage AC: | 400 V |
| Max. conductor cross section: | 4 mm ² |
| Protection class: | II |
| Type of protection: | IP54/IP66 |
| UL Type Rating: | not specified |

Dimensions

| | |
|---------|-------|
| Width: | 94 mm |
| Length: | 94 mm |
| Height: | 57 mm |

Material characteristics

| | |
|--|--------|
| UV-resistant: | yes |
| Halogen free: | yes |
| Flammability class according with UL94: | V2 |
| Glow-wire flammability according to EN 60695-2-11: | 960 °C |
| Industry quality: | yes |

mechanical properties

| | |
|--------------------|------------------------|
| Type of fastening: | Wall/ceiling mounting |
| Impact strength: | IK08 |
| Sealable: | yes |
| Stackable: | yes |
| Fastening: | internal fixing points |

Ambient conditions

| | |
|------------------------------|--------|
| max. relative humidity 25°C: | 95 % |
| max. relative humidity 40°C: | 50 % |
| Min. ambient temperature: | -25 °C |

Ambient conditions

| | |
|---------------------------|-------------------------|
| Max. ambient temperature: | 40 °C |
| 24h ambient temperature: | 35 °C |
| Installation location: | protected outdoor areas |

Material

| | |
|-----------------------|-----------------------------------|
| Base unit material: | Polycarbonate |
| Cover material: | Polycarbonate |
| Sealing material: | Polyurethane |
| Cover screw material: | Polyamide, glass-fibre reinforced |

Accessories

[19000201 - ASS-kl - External hinge set](#)

[19202001 - KS M20 - Combi set](#)

[19400101 - TK ABL - External fixing lugs kit](#)

Cable gland

