

Socket outlet combination  
**STV 1222-K**



## STV 1222-K

### Socket outlet combination

#### CUSTOMIZABLE

Productnumber: 73142201

Dimensions: 250 x 400 x 122 mm

Socket outlet combination, protection class IP44, ready for connection, according to EN 61439-3, high mechanical strength, temperature-resistant, can be combined

Cable insertions:

Top: Pre-embossing 2 x M20, 2 x M20/25, 3 x M32/40

Bottom: Pre-embossing 2 x M20, 2 x M20/25, 3 x M32/40

Left: Pre-embossing 4 x M20

Right: Pre-embossing 4 x M20

Rear: Pre-embossing 4 x M20/25

#### equipped with:

- 2 x Miniature circuit breaker B16A, 1-pin
- 1 x Miniature circuit breaker C 16 A, 3p
- 1 x Miniature circuit breaker C 32 A, 3p
- 1 x Residual Current Circuit Breaker (RCCB), 40/0.03A, 4-pole, type A
- 2 x SCHUKO® plug socket (on front), 230V
- 1 x CEE plug socket outlet (on front) 16A, 400V
- 1 x CEE plug socket outlet (on front) 32A, 400V

#### Accessories supplied:

Attachment bushes: 2x M25, 2x M32, sealing plugs, masking and labelling strips



## Technical Data

### Built-in devices

Residual Current Circuit Breaker (RCCB), 40/0.03A, 4-pole, type A:	1
Miniature circuit breaker B16A, 1-pin:	2
Miniature circuit breaker C 16 A, 3p:	1
Miniature circuit breaker C 32 A, 3p:	1
SCHUKO® plug socket (on front), 230V:	2
CEE plug socket outlet (on front) 16A, 400V:	1
CEE plug socket outlet (on front) 32A, 400V:	1

### electrical characteristics

Rated insulation voltage AC:	400 V
Protection class:	II
Type of protection:	IP44
Number of N-potentials:	1
Number of rows:	1
Number of modules per row:	12
with N terminal:	yes
with PE terminal:	yes

### Colours

Base unit colour:	grey
Cover colour:	grey

### Dimensions

Width:	250 mm
Length:	400 mm
Height:	122 mm

## Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	850 °C
Industry quality:	yes

## mechanical properties

Type of fastening:	Wall mounting
Impact strength:	IK08

## Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

## Material

Base unit material:	Polycarbonate, glass-fibre reinforced
Cover material:	Polycarbonate, glass-fibre reinforced
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced
Hinged window material:	Polycarbonate

## Cable gland

