

Empty enclosure

AK 14 L-g



AK 14 L-g

Empty enclosure

CUSTOMIZABLE

Productnumber: 73341001

Dimensions: 315 x 300 x 147 mm

Empty enclosure, protection class IP65, Plastic, certified by DLG (Ammonia resistance), $U_i=1000V$ AC, $U_i=1500V$ DC, for AK 14-56 small distribution boards, for individual expansion by adding standard rails or mounting plates

Box: Plastic, grey, Lid: Polycarbonate, grey, metric knockouts on top and bottom for universal cable insertions with cable glands and/or double membrane seals, pre-mounted with double membrane seals M20 at the top

Accessories supplied:

Double-membrane seals: 1x M20, 1x M25, 1x M32, Attachment bushes: 1x M40, sealing plugs, masking and labelling strips



Technical Data

electrical characteristics

Rated operating voltage AC:	400 V
Rated insulation voltage AC:	1000 V
Rated insulation voltage DC:	1500 V
Protection class:	II
Type of protection:	IP65
with N terminal:	no
with PE terminal:	no
UL Type Rating:	not specified

Colours

Base unit colour:	grey
Cover colour:	grey

Dimensions

Width:	315 mm
Length:	300 mm
Height:	147 mm
Inner length:	310 mm
Inner width:	295 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	850 °C
Industry quality:	yes

mechanical properties

Type of fastening:	Surface mounted
--------------------	-----------------

mechanical properties

Impact strength:	IK08
Type of top part:	Cover

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Installation location:	Indoors

Material

Base unit material:	Plastic
Cover material:	Polycarbonate

Certificates

Test mark:	DLG (Ammonia resistance)
------------	--------------------------

Accessories

[73383701 - AK3 AS - External hinge](#)

[73383801 - AK3 MPI 14 L - Mounting plate](#)

[73385001 - AK3 3/14 PE - Terminal rails](#)

[73385101 - AK3 6/21 PE - Terminal rails](#)

[73385201 - AK3 1/6/1 N - N-Module-Set](#)

Cable gland

