

Empty enclosure

## AK-F 14 L-t



### AK-F 14 L-t

Empty enclosure

CUSTOMIZABLE

Productnumber: 73351101

Dimensions: 315 x 300 x 147 mm

Empty enclosure, protection class IP65, Plastic, certified by DLG (Ammonia resistance),  $U_i=1000V$  AC,  $U_i=1500V$  DC, for AK 14-56 small distribution boards, for individual expansion by adding standard rails or mounting plates

**Box: Plastic, grey, Lid: Polycarbonate, transparent, open top/bottom sides for the use with various flanges or for the combination of several AK-F distributors via combination flange**

**Accessories supplied:**

**Double-membrane seals: 1x M16, 5x M20, 2x M25, 1x M32, 1x M40, sealing plugs, masking and labelling strips**



## Technical Data

### electrical characteristics

Rated operating voltage AC:	400 V
Rated insulation voltage AC:	1000 V
Rated insulation voltage DC:	1500 V
Protection class:	II
Type of protection:	IP65
UL Type Rating:	not specified

### Colours

Base unit colour:	grey
Cover colour:	transparent

### Dimensions

Width:	315 mm
Length:	300 mm
Height:	147 mm
Inner length:	310 mm
Inner width:	295 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	yes

### mechanical properties

Type of fastening:	Surface mounted
Impact strength:	IK08
Flange variant:	yes

### mechanical properties

Type of top part:	Cover
-------------------	-------

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

### Material

Base unit material:	Plastic
Cover material:	Polycarbonate

### Certificates

Test mark:	DLG (Ammonia resistance)
------------	--------------------------

## Accessories

[73382001 - AK3 FL00 - Flange for AK-F](#)

[73382101 - AK3 FL01 - Flange for AK-F](#)

[73382201 - AK3 FL02 - Flange for AK-F](#)

[73382801 - AK3 FL13 - Flange for AK-F](#)

[73382901 - AK3 KFL - Flange for AK-F](#)

[73383701 - AK3 AS - External hinge](#)

[73383801 - AK3 MPI 14 L - Mounting plate](#)

[73385001 - AK3 3/14 PE - Terminal rails](#)

[73385101 - AK3 6/21 PE - Terminal rails](#)

[73385201 - AK3 1/6/1 N - N-Module-Set](#)

**Cable gland**

