

Small distributions boards

# AK 09



## AK 09

### Small distributions boards

**CUSTOMIZABLE**

Productnumber: 73540901

Dimensions: 200 x 200 x 122 mm

Small distributions boards, protection class IP65, 1 row, 9 available modules, rated operational voltage: 400V AC, rated insulation voltage: 1000V AC, 1000V DC, metric knockouts on top and bottom for universal cable insertions with cable glands and/or double membrane seals, pre-mounted with double membrane seals M20 at the top, for standard installations indoors

**with PE/N terminal rail, each with 2 clamping points 16 mm<sup>2</sup> and 5 clamping points 6 mm<sup>2</sup>**

**Accessories supplied:**

**Double-membrane seals: 1x M20, 1x M32, sealing plugs, masking and labelling strips**



Reliable - The high protection class (IP65) and the robust, halogen-free design ensure reliable operation even in a tough industrial environment.

## Technical Data

### electrical characteristics

Rated operating voltage AC:	400 V
Rated insulation voltage AC:	1000 V
Rated insulation voltage DC:	1000 V
Protection class:	II
Type of protection:	IP65
Number of rows:	1
Number of modules:	9

### Colours

Base unit colour:	grey
Cover colour:	grey

### Dimensions

Width:	200 mm
Length:	200 mm
Height:	122 mm
Inner height:	95 mm

### Material characteristics

UV-resistant:	no
Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

### mechanical properties

Type of fastening:	Surface mounting
Impact strength:	IK07
Sealable:	yes

### mechanical properties

Cover screw torque:	1.2 Nm
Stackable:	yes

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	Indoors

### Material

Base unit material:	Polystyrene
Cover material:	Polystyrene
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced
Hinged window material:	Polycarbonate

## Accessories

[70610201 - AK SGA-1 - Lock fittings](#)

[70690201 - AK SGA-2 - Lock fittings](#)

[89603201 - MABF 150-3 - Mast/pipe fixing set](#)

[73540009 - AK KF 09 - Hinged window](#)

[79901201 - AK AS - Masking off strips](#)

[26242001 - BST M20 - Ventilation seal](#)

[26202001 - BST M20/sw - Ventilation seal](#)

## Cable gland

