

Small distributions boards

AKi 09



AKi 09

Small distributions boards

CUSTOMIZABLE

Productnumber: 73640901

Dimensions: 200 x 200 x 122 mm

Small distributions boards, protection class IP65, 1 row, 9 available modules, rated operational voltage: 400V AC, rated insulation voltage: 1000V AC, 1000V DC, metric knockouts on top and bottom for universal cable insertions with cable glands and/or double membrane seals, pre-mounted with double membrane seals M20 at the top, for installations in the industrial environment and protected outside areas

with PE/N terminal rail, each with 2 clamping points 16 mm² and 5 clamping points 6 mm²

Accessories supplied:

Double-membrane seals: 1x M20, 1x M32, sealing plugs, masking and labelling strips



Easy to install - PE/N terminal strip, flexible entries on the top and the generous spacing of the strip allow for especially convenient, rapid installation of the distributors.

Technical Data

electrical characteristics

Rated operating voltage AC:	400 V
Rated insulation voltage AC:	1000 V
Rated insulation voltage DC:	1000 V
Protection class:	II
Type of protection:	IP65
Number of rows:	1
Number of modules:	9

Colours

Base unit colour:	grey
Cover colour:	grey

Dimensions

Width:	200 mm
Length:	200 mm
Height:	122 mm
Inner height:	95 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

mechanical properties

Type of fastening:	Surface mounting
Impact strength:	IK08
Sealable:	yes

mechanical properties

Cover screw torque:	1.2 Nm
Stackable:	yes

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	80 °C
24h ambient temperature:	60 °C
Installation location:	protected outdoor areas

Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate, glass-fibre reinforced
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced
Hinged window material:	Polycarbonate

Accessories

[70610201 - AK SGA-1 - Lock fittings](#)

[70690201 - AK SGA-2 - Lock fittings](#)

[89603201 - MABF 150-3 - Mast/pipe fixing set](#)

[73540009 - AK KF 09 - Hinged window](#)

[79901201 - AK AS - Masking off strips](#)

[26242001 - BST M20 - Ventilation seal](#)

[26202001 - BST M20/sw - Ventilation seal](#)

Cable gland

