

Socket outlet combination

AKi 1-1S



AKi 1-1S

Socket outlet combination

CUSTOMIZABLE

Productnumber: 74111101

Dimensions: 300 x 150 x 132 mm

Socket outlet combination, protection class IP44, with integrated, pre-wired sockets, high mechanical resilience, non-sensitive to temperature, combinable, halogen-free

Cable insertions:

Top: Pre-embossing 15 x M20, 2 x M20/25, 1 x M32/40

Bottom: Pre-embossing 15 x M20, 2 x M20/25, 1 x M32/40

Left: Pre-embossing 4 x M20, 1 x M25/32

Right: Pre-embossing 4 x M20, 1 x M25/32

equipped with:

- 8 x SCHUKO® plug socket (on front), 230V

Accessories supplied:

Double-membrane seals: 1x M20, 1x M25, 1x M32, Attachment bushes: 1x M40, sealing plugs, masking and labelling strips



Technical Data

Built-in devices

SCHUKO® plug socket (on front), 230V:	8
---------------------------------------	---

electrical characteristics

Rated insulation voltage AC:	400 V
------------------------------	-------

Protection class:	II
-------------------	----

Type of protection:	IP44
---------------------	------

Number of rows:	0
-----------------	---

Colours

Base unit colour:	grey
-------------------	------

Cover colour:	grey
---------------	------

Dimensions

Width:	300 mm
--------	--------

Length:	150 mm
---------	--------

Height:	132 mm
---------	--------

Material characteristics

UV-resistant:	yes
---------------	-----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	V2
---	----

Glow-wire flammability according to EN 60695-2-11:	850 °C
--	--------

Industry quality:	yes
-------------------	-----

mechanical properties

Type of fastening:	Wall mounting
--------------------	---------------

Impact strength:	IK08
------------------	------

Ambient conditions

max. relative humidity 25°C:	95 %
------------------------------	------

Ambient conditions

max. relative humidity 40°C:	50 %
------------------------------	------

Min. ambient temperature:	-35 °C
---------------------------	--------

Max. ambient temperature:	40 °C
---------------------------	-------

24h ambient temperature:	35 °C
--------------------------	-------

Installation location:	protected outdoor areas
------------------------	-------------------------

Material

Base unit material:	Polycarbonate
---------------------	---------------

Cover material:	Polycarbonate, glass-fibre reinforced
-----------------	---------------------------------------

Sealing material:	Polyurethane
-------------------	--------------

Cover screw material:	Polyamide, glass-fibre reinforced
-----------------------	-----------------------------------

Cable gland

