

Socket outlet combination

## AKi 1-3S



### AKi 1-3S

Socket outlet combination

CUSTOMIZABLE

Productnumber: 74113101

Dimensions: 300 x 150 x 132 mm

Socket outlet combination, protection class IP44, with integrated, pre-wired sockets, high mechanical resilience, non-sensitive to temperature, combinable, halogen-free

Cable insertions:

Top: Pre-embossing 15 x M20, 2 x M20/25, 1 x M32/40

Bottom: Pre-embossing 15 x M20, 2 x M20/25, 1 x M32/40

Left: Pre-embossing 4 x M20, 1 x M25/32

Right: Pre-embossing 4 x M20, 1 x M25/32

equipped with:

- 4 x SCHUKO® plug socket (on front), 230V
- 2 x CEE plug socket outlet (on front) 16A, 400V

Accessories supplied:

Double-membrane seals: 1x M20, 1x M25, 1x M32, Attachment bushes: 1x M40, sealing plugs, masking and labelling strips



## Technical Data

### Built-in devices

SCHUKO® plug socket (on front), 230V:	4
CEE plug socket outlet (on front) 16A, 400V:	2

### electrical characteristics

Rated insulation voltage AC:	400 V
Protection class:	II
Type of protection:	IP44
Number of rows:	0

### Colours

Base unit colour:	grey
Cover colour:	grey

### Dimensions

Width:	300 mm
Length:	150 mm
Height:	132 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	850 °C
Industry quality:	yes

### mechanical properties

Type of fastening:	Wall mounting
Impact strength:	IK08

## Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

## Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate, glass-fibre reinforced
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced

## Cable gland

