

Null conductor terminal

AK N 47-S

AK N 47-S

Null conductor terminal

Productnumber: 79004701

Dimensions: 242 x 25 x 23 mm

Auxiliary terminal, for subsequent attachment to AK PE/N basic terminals from AK 14

**4 x 7-pole,, with each 2 clamping points 16 mm²,
5 clamping points 6 mm²**



Technical Data

electrical characteristics

Rated operating voltage AC:	400 V
Number of poles:	4
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Strip length:	12 mm
Connection 1: Clamping points per pole:	7
Connection 1: Suitable for Cu conductors:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	6 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	16 mm ²
Connection 2: Connection type:	Screws
Connection 2: Suitable for Cu conductors:	1
Connection 2: Connectable conductor cross-section, single-wire (min):	1.5 mm ²
Connection 2: Connectable conductor cross-section, single-wire (max):	6 mm ²

Dimensions

Width:	242 mm
Length:	25 mm
Height:	23 mm

Material characteristics

Burning behaviour in accordance with UL 50/UL 746C:	V2
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	no

mechanical properties

Connection 1: Tightening moment:	1.4 Nm
----------------------------------	--------

mechanical properties

Connection 2: Tightening torque:	1.4 Nm
----------------------------------	--------

Material

Insulating body material:	Thermoplastic
---------------------------	---------------