

Terminal rails

AK 05 PEN-S



AK 05 PEN-S

Terminal rails

Productnumber: 79020501

Dimensions: 103 x 26 x 13 mm

PE/N terminal rail, for installation in AK/AKi compact small distribution board as additional terminals or for replacement.

PE/N-terminal each with 2 clamping points of 16 mm² and 3 clamping points of 6 mm²

Technical Data

electrical characteristics

Rated operating voltage AC:	400 V
Number of poles:	2
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Strip length:	12 mm
Connection 1: Clamping points per pole:	5
Connection 1: Suitable for Cu conductors:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	6 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	16 mm ²
Connection 2: Connection type:	Screws
Connection 2: Suitable for Cu conductors:	1
Connection 2: Connectable conductor cross-section, single-wire (min):	1.5 mm ²
Connection 2: Connectable conductor cross-section, single-wire (max):	6 mm ²

Dimensions

Width:	103 mm
Length:	26 mm
Height:	13 mm

Material characteristics

Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	no

mechanical properties

Connection 1: Tightening moment:	1.4 Nm
Connection 2: Tightening torque:	1.4 Nm

Material

Insulating body material:	Thermoplastic
---------------------------	---------------

Accessories

[79541301 - SR NS35 - Screw set](#)