

Terminal block

KLS N 35



KLS N 35

Terminal block

Productnumber: 79090501

Dimensions: 48 x 42 x 25 mm

PE/N terminal block for mounting onto 35 mm standard rail, e.g. in meter housings

N terminal (blue) 3 x 25 mm², 2 x 16 mm²



Technical Data

electrical characteristics

Rated operating voltage AC:	690 V
Number of poles:	1
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	5
Connection 1: Suitable for Cu conductors:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	2.5 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	25 mm ²
Connection 2: Connection type:	Screws
Connection 2: Suitable for Cu conductors:	1
Connection 2: Connectable conductor cross-section, single-wire (min):	1 mm ²
Connection 2: Connectable conductor cross-section, single-wire (max):	16 mm ²

Dimensions

Width:	48 mm
Length:	42 mm
Height:	25 mm

Material characteristics

Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	no

mechanical properties

Connection 2: Tightening torque:	2.5 Nm
----------------------------------	--------

Material

Insulating body material:	Thermoplastic
---------------------------	---------------

Certificates

Test mark:	VDE (DIN 60998-1/-2-1 (VDE 0613-1/-2-1))
------------	--