

Terminal block

## **Abox 250/350 KLS-25<sup>2</sup>/35<sup>2</sup>**

### **Abox 250/350 KLS-25<sup>2</sup>/35<sup>2</sup>**

**Terminal block**

Productnumber: 84003501

Dimensions: 277 x 66 x 18 mm

Connecting terminal acc. to DIN EN 60998 (VDE 0613),  $U_i=690V$

**5-pole - 35 mm<sup>2</sup>**



## Technical Data

### electrical characteristics

Rated operating voltage AC:	690 V
Rated current:	125 A
Number of poles:	5
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	4
Connection 1: Suitable for Cu conductors:	1
Connection 1: Connectable conductor cross-section, single-wire (min):	10 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, single-wire (max):	35 mm <sup>2</sup>

### Dimensions

Width:	277 mm
Length:	66 mm
Height:	18 mm

### Material characteristics

Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	no

### mechanical properties

Connection 1: Tightening moment:	4 Nm
----------------------------------	------

### Material

Insulating body material:	Thermoplastic
---------------------------	---------------

### Certificates

Test mark:	VDE (DIN 60998-1/-2-1 (VDE 0613-1/-2-1))
------------	--