


Junction box

WKE 202 RK

This product is outdated. To the successor product: <https://www.spelsberg.com/p/86228201>



WKE 202 RK

Junction box

CUSTOMIZABLE

Productnumber: 86220201

Dimensions: 115 x 115 x 93 mm

Junction box, protection class IP66, $U_i=450$ V AC, certified by VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22)), M32, (2 side), external fixing lugs, with E30 electrical functional integrity according to DIN 4102 Part 12, enclosure and terminal block are made from halogen-free special thermosetting plastic

orange, Connection box 5-pole, clamping capacity per pole 2 x 0.5 - 6 mm²

**Accessories supplied:
2 off cable glands M32, sealing range 17 - 26 mm, Wall plug set \varnothing 6 mm**



Technical Data

electrical characteristics

Rated insulation voltage AC:	450 V
Rated insulation voltage DC:	450 V
Min. conductor cross section:	0,5 mm ²
Max. conductor cross section:	6 mm ²
Protection class:	II
Type of protection:	IP66
secured junction:	no
Circuit integrity class:	E30
Number of poles (T-piece):	0
Number of poles (feed-through):	5
UL Type Rating:	not specified
Number of fuses in T-piece:	0

Colours

Base unit colour:	orange
Cover colour:	orange

Additional features

Range of application:	Connectors and T-pieces
-----------------------	-------------------------

Dimensions

Width:	115 mm
Length:	115 mm
Height:	93 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V0

Material characteristics

Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK08
Sealable:	no
Cover screw torque:	2.5 Nm
Fastening:	external fixing lugs

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

Material

Base unit material:	Duroplast
Cover material:	Duroplast
Sealing material:	Polyurethane
Cover screw material:	Stainless steel V2A

Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
------------	---

Accessories

[86040001 - WKE 200 ABL - External attachment set](#)

Cable gland

