


Junction box

WKE 204 RK

This product is outdated. To the successor product: <https://www.spelsberg.com/p/86228401>



WKE 204 RK

Junction box

CUSTOMIZABLE

Productnumber: 86220401

Dimensions: 115 x 115 x 93 mm

Junction box, protection class IP66, $U_i=450$ V AC, certified by VDE (DIN EN 61439-1/-2 (VDE 0660-600-1/-2)), M25, (3 side), external fixing lugs, with E30 electrical functional integrity according to DIN 4102 Part 12, enclosure and terminal block are made from halogen-free special thermosetting plastic

orange, junction box with fused branch, connection box 3-pole, junction box 3-pole, number of clampable wires per pole 4 x 0.5 - 4mm², clamping capacity per terminal point 1 x 0.5 - 4mm², fuse holder (20 x 5mm) max. 6.3 A

Accessories supplied:

3 cable glands M25 (6 - 15mm), wall plug set \varnothing 6 mm



Technical Data

electrical characteristics

Rated insulation voltage AC:	450 V
Rated insulation voltage DC:	450 V
Min. conductor cross section:	0,5 mm ²
max. wire cross section (wire branching):	4 mm ²
Min. conductor cross section:	0,5 mm ²
Max. conductor cross section:	4 mm ²
Protection class:	II
Type of protection:	IP66
secured junction:	yes
Circuit integrity class:	E30
Number of poles (T-piece):	3
Number of poles (feed-through):	3
UL Type Rating:	not specified
Number of fuses in T-piece:	1

Colours

Base unit colour:	orange
Cover colour:	orange

Additional features

Range of application:	Fused T-piece
-----------------------	---------------

Dimensions

Width:	115 mm
Length:	115 mm
Height:	93 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes

Material characteristics

Flammability class according with UL94:	V0
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

mechanical properties

Type of fastening:	Wall/ceiling mounting
Impact strength:	IK08
Sealable:	no
Cover screw torque:	2.5 Nm
Fastening:	external fixing lugs

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

Material

Base unit material:	Duroplast
Cover material:	Duroplast
Sealing material:	Polyurethane
Cover screw material:	Stainless steel V2A

Certificates

Test mark:	VDE (DIN EN 61439-1/-2 (VDE 0660-600-1/-2))
------------	---

Accessories

[86040001 - WKE 200 ABL - External attachment set](#)

Cable gland

