

Receptacle

## HW 050



### HW 050

#### Receptacle

Productnumber: 92005001

Dimensions: 68 x 68 x 50 mm

Cavity wall receptacle, flame resistant, universal socket for plate thicknesses from 1 to 40 mm with moulded patented combi jumpers and punching tool, device screw spacing 60 mm

**drilled hole Ø 68 mm, 50 mm deep, with coated, patented combi bridges**



## Technical Data

### electrical characteristics

Rated insulation voltage AC:	400 V
Type of protection:	IP30
UL Type Rating:	not specified

### Dimensions

Width:	68 mm
Length:	68 mm
Height:	50 mm
Inner height:	48 mm

### Material characteristics

Halogen free:	no
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	850 °C
Industry quality:	no

### Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	Indoors

### Material

Base unit material:	Plastic
Cover material:	Polypropylene

## Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
------------	-------------------------------------------

## Accessories

[97910501 - ES-10 - Installation screw](#)

[97910601 - ES-18 - Installation screw](#)

[97910701 - ES-25 - Installation screw](#)