

Branch socket

HW 065 H



HW 065 H

Branch socket

Productnumber: 92026501

Dimensions: 68 x 68 x 65 mm

Cavity wall equipment junction box, flame-retardant and halogen-free, with enlarged terminal compartment, universal box for panel thicknesses 1- 40 mm, with punching tool, 60 mm equipment screw spacing, halogen-free

drilled hole Ø 68 mm, 65 mm deep, with coated, patented combi bridges



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Type of protection:	IP30
UL Type Rating:	not specified

Colours

Base unit colour:	white
-------------------	-------

Dimensions

Width:	68 mm
Length:	68 mm
Height:	65 mm
Inner height:	63 mm

Material characteristics

Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	no

Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	Indoors

Material

Base unit material:	Plastic
---------------------	---------

Material

Cover material:	Polypropylene
-----------------	---------------

Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
------------	---

Accessories

[97910501 - ES-10 - Installation screw](#)

[97910601 - ES-18 - Installation screw](#)

[97910701 - ES-25 - Installation screw](#)