

Double socket

## HW 050/2 WD



### HW 050/2 WD

**Double socket**

Productnumber: 92335001

Dimensions: 68 x 139 x 50 mm

Cavity wall double socket, flame resistant, for plate thicknesses from 1 to 40 mm, with moulded patented combi jumpers and punching tool, device screw spacing 60 mm

**with closed membrane entries, drilled hole Ø 2 x 68 mm, 50 mm deep, Combination spacing 71 mm**

IP30

400V  
AC

## Technical Data

### electrical characteristics

Rated insulation voltage AC:	400 V
Type of protection:	IP30
UL Type Rating:	not specified

### Dimensions

Width:	68 mm
Length:	139 mm
Height:	50 mm

### Material characteristics

Halogen free:	no
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	850 °C
Industry quality:	no

### Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	Indoors

### Material

Base unit material:	Plastic
Cover material:	Polypropylene

## Accessories

[97910501 - ES-10 - Installation screw](#)

[97910601 - ES-18 - Installation screw](#)

[97910701 - ES-25 - Installation screw](#)