

Junction Box

## HW 120



### HW 120

#### Junction Box

Productnumber: 92512001

Dimensions: 120 x 120 x 65 mm

Cavity wall connection socket, flame resistant, for plate thicknesses from 7 to 35 mm, for terminals up to 4 mm<sup>2</sup>, including white sealing cap

**Drilled hole Ø 120 mm, 65 mm deep**

IP30 400V  
AC

## Technical Data

### electrical characteristics

Rated insulation voltage AC:	400 V
Type of protection:	IP30
UL Type Rating:	not specified

### Dimensions

Width:	120 mm
Length:	120 mm
Height:	65 mm

### Material characteristics

Halogen free:	no
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	850 °C
Industry quality:	no

### Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	Indoors

### Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

## Accessories

[97910501 - ES-10 - Installation screw](#)

[97910601 - ES-18 - Installation screw](#)

[97910701 - ES-25 - Installation screw](#)