

Conduit elbow

ROK 20



ROK 20

Conduit elbow

Productnumber: 97042501

Dimensions: 33 x 52,5 x 54 mm

Conduit elbow, rated insulation voltage: 400V AC,
Halogen free, Number of 30° insertions: 1

**for 30° insertion to insert into conduit ferrule
(small) 97051801, M20, sealing range M20**



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Suitable for:	Concrete construction

Dimensions

Width:	33 mm
Length:	52.5 mm
Height:	54 mm

Material characteristics

Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

Accessories

[97911501 - DH 55 - ceiling hook](#)

[97911601 - DH 90 - ceiling hook](#)

[97911801 - DH 65 - ceiling hook](#)

[97924001 - NAS-AL - IBT Accessories](#)

[97924201 - NA-AL - IBT Accessories](#)

[97924301 - NA-AL/gl - IBT Accessories](#)