

Conduit elbow

ROK 25



ROK 25

Conduit elbow

Productnumber: 97043001

Dimensions: 48 x 76,5 x 71,5 mm

Conduit elbow, rated insulation voltage: 400V AC,
Halogen free, Number of 30° insertions: 1

**for 30° insert to insert into conduit ferrule
(medium) 97052301, M25, sealing range M25**



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Suitable for:	Concrete construction

Dimensions

Width:	48 mm
Length:	76.5 mm
Height:	71.5 mm

Material characteristics

Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

Accessories

[97911501 - DH 55 - ceiling hook](#)

[97911601 - DH 90 - ceiling hook](#)

[97911801 - DH 65 - ceiling hook](#)

[97924001 - NAS-AL - IBT Accessories](#)

[97924201 - NA-AL - IBT Accessories](#)

[97924301 - NA-AL/gl - IBT Accessories](#)