

Conduit ferrule

ROP 40



ROP 40

Conduit ferrule

Productnumber: 97053701

Dimensions: 49 x 64 x 45 mm

Conduit ferrule, with bottom section, to take various conduit diameters, rated insulation voltage: 400V AC, Halogen free

adhesive fixing or nail installation, sealing range M40, support spar compatible



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Suitable for:	Concrete construction

Dimensions

Width:	49 mm
Length:	64 mm
Height:	45 mm

Material characteristics

Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

mechanical properties

Type of fastening:	adhesive fixing or nail installation
--------------------	--------------------------------------

Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

Accessories

[97924001 - NAS-AL - IBT Accessories](#)

[97924201 - NA-AL - IBT Accessories](#)

[97924301 - NA-AL/gl - IBT Accessories](#)