

Universal outlet cleats

DAL 1

DAL 1

Universal outlet cleats

Productnumber: 97070501

Dimensions: 49 x 171 x 35 mm

Universal outlet cleats, usable as a ceiling outlet with a large tolerance compensation, protection class IP00, rated insulation voltage: 400V AC, Halogen free

DAL 1 and DAL 2 can be combined next to each other and one behind the other without tools, adhesive fixing or nail installation, sealing range M20 - M25



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Type of protection:	IP00
Suitable for:	Concrete construction
UL Type Rating:	not specified

Dimensions

Width:	49 mm
Length:	171 mm
Height:	35 mm

Material characteristics

Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

mechanical properties

Type of fastening:	adhesive fixing or nail installation
--------------------	--------------------------------------

Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

Accessories

[23162001 - VST M20/or - Sealing plugs](#)

[23162501 - VST M25/or - Sealing plugs](#)

[97924001 - NAS-AL - IBT Accessories](#)

[97924201 - NA-AL - IBT Accessories](#)

[97924301 - NA-AL/gl - IBT Accessories](#)