

Conduit elbow set

## ROK 20 S



### ROK 20 S

#### Conduit elbow set

Productnumber: 97072001

Dimensions: 63 x 35 x 62 mm

Conduit elbow set, consisting of conduit ferrule with bottom section and conduit elbow 30°, rated insulation voltage: 400V AC, Halogen free, Number of 30° insertions: 1

**3-part, adhesive fixing or nail installation, sealing range M20, support spar compatible**



## Technical Data

### electrical characteristics

Rated insulation voltage AC:	400 V
Suitable for:	Concrete construction

### Dimensions

Width:	63 mm
Length:	35 mm
Height:	62 mm

### Material characteristics

Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

### mechanical properties

Type of fastening:	adhesive fixing or nail installation
--------------------	--------------------------------------

### Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

### Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

## Accessories

[97911501 - DH 55 - ceiling hook](#)

[97911601 - DH 90 - ceiling hook](#)

[97911801 - DH 65 - ceiling hook](#)

[97924001 - NAS-AL - IBT Accessories](#)

[97924201 - NA-AL - IBT Accessories](#)

[97924301 - NA-AL/gl - IBT Accessories](#)