

Dome box

U 71 KUD



U 71 KUD

Dome box

Productnumber: 97104701

Dimensions: 71 x 71 x 91 mm

Dome box, can also be used as a sealing box, 2 screw bosses with 60 mm screw spacing, combinable with normal 71 mm spacing, fully insulated cable transition, suitable for all types of formwork and opposing formwork, protection class IP30, rated insulation voltage: 400V AC, Halogen free, Number of 45° insertions: 4

2-part, magnet and nail installation, membrane for perforation, sealing range M16 - M25, support spar compatible



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Type of protection:	IP30
Suitable for:	Concrete construction
UL Type Rating:	not specified

Colours

Cover colour:	other
---------------	-------

Dimensions

Width:	71 mm
Length:	71 mm
Height:	91 mm

Material characteristics

Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

mechanical properties

Type of fastening:	magnet and nail installation
--------------------	------------------------------

Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

Accessories

- [97925001 - HFL - IBT Accessories](#)
- [97929901 - HM-UNI - IBT Accessories](#)
- [97911601 - DH 90 - ceiling hook](#)
- [97910001 - VD 75 - sealing plate](#)
- [97912201 - DH 90-M5 - ceiling hook](#)
- [19599501 - LFR - Stepped drill](#)
- [92510101 - HW VD-60 - sealing plate](#)
- [97022001 - RVB 20 - Conduit coupling](#)
- [97022501 - RVB 25 - Conduit coupling](#)
- [97023201 - RVB 32 - Conduit coupling](#)
- [97024001 - RVB 40 - Conduit coupling](#)
- [97174801 - U 71 KP-M5 - Dome](#)
- [97810001 - IBT LZA-OE - Hole punch](#)
- [97811801 - IBT LZA-18 - Hole punch](#)
- [97812301 - IBT LZA-23 - Hole punch](#)
- [97891401 - IBT STE-LZA/14 - Punch set](#)
- [97891801 - IBT STE-LZA/18 - Punch set](#)
- [97892301 - IBT STE-LZA/23 - Punch set](#)
- [97910201 - U 71 VDF - sealing plate](#)
- [97910401 - U 71 VDS - sealing plate](#)
- [97910501 - ES-10 - Installation screw](#)
- [97910601 - ES-18 - Installation screw](#)
- [97910701 - ES-25 - Installation screw](#)
- [97911001 - GWB - Thread bottom](#)
- [97915501 - WED - Expansion mandrel](#)
- [97920501 - IBT ST - Plug](#)
- [97921001 - VBN - Compound nipple](#)
- [97921201 - VB 71 - IBT Accessories](#)
- [97921301 - VB 80/85 - IBT Accessories](#)
- [97921401 - VB 90 - IBT Accessories](#)
- [97921501 - VB 105 - IBT Accessories](#)
- [97924001 - NAS-AL - IBT Accessories](#)
- [97924201 - NA-AL - IBT Accessories](#)

[97924301 - NA-AL/gl - IBT Accessories](#)
[97926001 - ANSW - IBT Accessories](#)
[97953001 - U 71 BSK-NA - blank base](#)
[97953002 - U 71 BSK-2 - blank base](#)
[97953601 - STH-ELP - Cartridge insert](#)
[97953801 - U 71 BSK-K - blank base](#)
[97953901 - U 71 BSK - blank base](#)
[97957001 - STH 70 - Support spar](#)
[97959001 - STH 90 - Support spar](#)
[97960001 - STH 100 - Support spar](#)
[97961001 - STH 110 - Support spar](#)
[97963001 - STH 130 - Support spar](#)
[97964001 - STH 140 - Support spar](#)
[97965001 - STH 150 - Support spar](#)
[97967001 - STH 170 - Support spar](#)
[97969001 - STH 190 - Support spar](#)
[97973001 - STH 230 - Support spar](#)
[97974001 - STH 240 - Support spar](#)
[97979001 - STH 290 - Support spar](#)

Cable gland

$$2x \leq \varnothing 25 \text{ mm}$$

