


Large conduit box

U 71 K GRO



U 71 K GRO

Large conduit box

Productnumber: 97276001

Dimensions: 71 x 71 x 76 mm

Large conduit box , 4 screw bosses with 60 mm screw spacing, combinable with normal 71 mm spacing, fully insulated cable transition, suitable for all types of formwork and opposing formwork, protection class IP30, rated insulation voltage: 400V AC, certified by VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22)), Halogen free

2-part, adhesive fixing or nail installation, membrane for perforation, sealing range M16 - M40, support spar compatible



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Type of protection:	IP30
Suitable for:	Concrete construction
UL Type Rating:	not specified

Colours

Cover colour:	other
---------------	-------

Dimensions

Width:	71 mm
Length:	71 mm
Height:	76 mm

Material characteristics

Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

mechanical properties

Type of fastening:	adhesive fixing or nail installation
--------------------	--------------------------------------

Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

Certificates

Test mark:	VDE (DIN EN 60670-1/-22 (VDE 0606-1/-22))
------------	---

Accessories

- [97924801 - KR - IBT Accessories](#)
- [97910001 - VD 75 - sealing plate](#)
- [92510101 - HW VD-60 - sealing plate](#)
- [97174801 - U 71 KP-M5 - Dome](#)
- [97910201 - U 71 VDF - sealing plate](#)
- [97910401 - U 71 VDS - sealing plate](#)
- [97910501 - ES-10 - Installation screw](#)
- [97910601 - ES-18 - Installation screw](#)
- [97910701 - ES-25 - Installation screw](#)
- [97911001 - GWB - Thread bottom](#)
- [97921001 - VBN - Compound nipple](#)
- [97921201 - VB 71 - IBT Accessories](#)
- [97921301 - VB 80/85 - IBT Accessories](#)
- [97921401 - VB 90 - IBT Accessories](#)
- [97921501 - VB 105 - IBT Accessories](#)
- [97924001 - NAS-AL - IBT Accessories](#)
- [97924201 - NA-AL - IBT Accessories](#)
- [97924301 - NA-AL/gl - IBT Accessories](#)
- [97926001 - ANSW - IBT Accessories](#)
- [97953001 - U 71 BSK-NA - blank base](#)
- [97953002 - U 71 BSK-2 - blank base](#)
- [97953601 - STH-ELP - Cartridge insert](#)
- [97953801 - U 71 BSK-K - blank base](#)
- [97953901 - U 71 BSK - blank base](#)
- [97957001 - STH 70 - Support spar](#)
- [97959001 - STH 90 - Support spar](#)
- [97960001 - STH 100 - Support spar](#)
- [97961001 - STH 110 - Support spar](#)
- [97963001 - STH 130 - Support spar](#)
- [97964001 - STH 140 - Support spar](#)
- [97965001 - STH 150 - Support spar](#)
- [97967001 - STH 170 - Support spar](#)
- [97969001 - STH 190 - Support spar](#)

[97973001 - STH 230 - Support spar](#)

[97974001 - STH 240 - Support spar](#)

[97979001 - STH 290 - Support spar](#)

Cable gland

$4x \leq \varnothing 37 \text{ mm}$

