

Deep box

U 71 TD-44



U 71 TD-44

Deep box

Productnumber: 97292501

Dimensions: 71 x 71 x 49 mm

Deep box, as top enclosure for all U 71 boxes when using large concrete conduits up to M25, screw spacing 60 mm, provides additional installation space of 44mm in depth, protection class IP00, rated insulation voltage: 400V AC, Halogen free

attachable, membrane for perforation, sealing range M16 - M25



Technical Data

electrical characteristics

Rated insulation voltage AC:	400 V
Type of protection:	IP00
Suitable for:	Concrete construction
UL Type Rating:	not specified

Colours

Cover colour:	other
---------------	-------

Dimensions

Width:	71 mm
Length:	71 mm
Height:	49 mm

Material characteristics

Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

mechanical properties

Type of fastening:	attachable
--------------------	------------

Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

Cable gland

$6x \leq \varnothing 25 \text{ mm}$
 $2x \leq \varnothing 20 \text{ mm}$

