Flange

GFL 221-m

GFL 221-m

Flange

Productnumber: 07222101
Dimensions: 175 x 119 x 15 mm

Flange with metric knockouts, 2 x flange connectors (GFV)

Pre-stamped for cable insertion: 1x M50/M40, 4x M25/M20

IP65

Created at 12.10.2024. All statements without guarantee. We reserve the right to make improvements to technical progress.
Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299

Technical Data

electrical characteristics

Type of protection:	IP65
UL Type Rating:	3R

Colours

Accessory colour:	light grey

Dimensions

Width:	175 mm
Length:	119 mm
Height:	15 mm
Weight:	0.12 kg

Material characteristics

UV-resistant:	yes

Ambient conditions

Installation location:	protected outdoor areas

Sales Information

EAN:	4013902858828
Packing Unit Code:	C62
ETIM Class:	EC000211
Custom tariff number:	85389099

Material

Accessory material:	Polycarbonate, glass-fibre reinforced

Created at 12.10.2024. All statements without guarantee. We reserve the right to make improvements to technical progress.
Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299