Flange

GFL 331-m

GFL 331-m

Flange

Productnumber: 07233101
Dimensions: 275 x 119 x 15 mm

Flange with metric knockouts, 2 x flange connectors (GFV)

Pre-stamped for cable insertion: 17x M20/M16

IP65

Technical Data

electrical characteristics

Type of protection:	IP65
UL Type Rating:	3R

Colours

Accessory colour:	light grey

Dimensions

Width:	275 mm
Length:	119 mm
Height:	15 mm
Weight:	0.18 kg

Material characteristics

UV-resistant:	yes

Ambient conditions

Installation location:	protected outdoor areas

Sales Information

EAN:	4013902858842
Packing Unit Code:	C62
ETIM Class:	EC000211
Custom tariff number:	85389099

Material

Accessory material:	Polycarbonate, glass-fibre reinforced

Created at 12.10.2024. All statements without guarantee. We reserve the right to make improvements to technical progress.
Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299