Twist plug

WST M32

WST M32

Twist plug

Productnumber: 20343201
Dimensions: 37,5 x 37,5 x 25 mm

Twist plug, IP54, M_ x 1.5 mm, with closed sealing membrane, grey

Sealing range 17 - 24 mm, Thread length 14 mm

IP54

Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299

Technical Data

electrical characteristics

Type of protection:	IP54

Colours

Accessory colour:	light grey

Dimensions

Width:	37.5 mm
Length:	37.5 mm
Height:	25 mm

Material characteristics

UV-resistant:	no
Halogen free:	yes
Industry quality:	no

mechanical properties

for wall thickness max:	11 mm
for sealing range min:	11 mm
for sealing range max:	22 mm
for wall thickness min:	1 mm

Ambient conditions

Installation location:	Indoors

Created at 02.05.2024. All statements without guarantee. We reserve the right to make improvements to technical progress.
Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299