Double-membrane seals

DMS M20/sw

DMS M20/sw

Double-membrane seals

Productnumber: 26002001
Dimensions: 25,2 x 25,2 x 13,4 mm

Double membrane seals, IP66, with two sealing membranes, closed, thermoplastic elastomer (TPE), for wall thicknesses 1.5 - 4.5 mm, black

Sealing range 7 - 13 mm

IP66

Created at 12.10.2024. All statements without guarantee. We reserve the right to make improvements to technical progress.
Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299

Technical Data

electrical characteristics

Type of protection:	IP66

Colours

Accessory colour:	deep black

Dimensions

Width:	25.2 mm
Length:	25.2 mm
Height:	13.4 mm
Nominal size:	M20
Weight:	0.0032 kg

Material characteristics

UV-resistant:	yes
Halogen free:	yes

mechanical properties

for sealing range min:	7 mm
for sealing range max:	13 mm

Ambient conditions

Installation location:	protected outdoor areas

Sales Information

EAN:	4013902932603
Packing Unit Code:	C62
ETIM Class:	EC000451
Custom tariff number:	39269097

Material

Accessory material:	Rubber

Created at 12.10.2024. All statements without guarantee. We reserve the right to make improvements to technical progress.
Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299