Double-membrane seals

DMS M25/w

DMS M25/w

Double-membrane seals

Productnumber: 26012501
Dimensions: 29,7 x 29,7 x 13,6 mm

Double membrane seals, IP66, with two sealing membranes, closed, thermoplastic elastomer (TPE), for wall thicknesses 1.5 - 4.5 mm, white

Sealing range 9 - 17 mm

IP66

Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299

Technical Data

electrical characteristics

Type of protection:	IP66

Colours

Accessory colour:	clear white

Dimensions

Width:	29.7 mm
Length:	29.7 mm
Height:	13.6 mm
Nominal size:	M25

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Industry quality:	no

mechanical properties

for wall thickness max:	4.5 mm
for sealing range min:	9 mm
for sealing range max:	17 mm
for wall thickness min:	1.5 mm

Ambient conditions

Installation location:	protected outdoor areas

Material

Accessory material:	Rubber

Created at 19.04.2024. All statements without guarantee. We reserve the right to make improvements to technical progress.
Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299