Conduit connector

RST M32

RST M32

Conduit connector

Productnumber: 28843201
Dimensions: 46 x 41 x 40 mm

Pipe socket to take smooth pipes, with locknut, polystyrene, grey

for conduits with an external diameter of 32 mm

IP54

Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299

Technical Data

electrical characteristics

Type of protection:	IP54

Colours

Accessory colour:	light grey

Dimensions

Width:	46 mm
Length:	41 mm
Height:	40 mm
Weight:	0.016 kg

Material characteristics

UV-resistant:	no
Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C

Ambient conditions

Installation location:	Indoors

Sales Information

EAN:	4013902921508
Packing Unit Code:	C62
ETIM Class:	EC000451
Custom tariff number:	39269097

Created at 12.10.2024. All statements without guarantee. We reserve the right to make improvements to technical progress.
Günther Spelsberg GmbH + Co. KG
Im Gewerbepark 1 · D-58579 Schalksmühle · Telefon: +49 (0) 23 55 / 892-0 · Telefax: +49 (0) 23 55 / 892-299